

MSC AC SPLICE CLOSURE WITH TRAYS MST

The FOCUS-MSC-AC watertight closure (IP68, IEC 529) was created for the management and the splicing of high capacity fiber optic cables. Differently to the other Optotec's closure, it accommodates FOCS MST trays, up to max. 8. FOCUS MST trays are splice only and they have a maximum capacity of 96 f.o. joints, both heath shrinkable FIBERTERM and mechanical FIBERCLIP.

In the upper part of the tray it is possible to allocate PLC.



For in line closures, branch joints and pot-head

- aerial networks, on pole and on wall
- underground networks: inside handholes / manholes

0-ring closing system

- High quality thermoplastic material watertight - BASE and DOME (IP68, IEC 529) with clamp and
- Management Capability of various types of tube cables, slotted core and ribbon

Easy access to the junction area through CLAMP opening equipped with a guided locking

The BASE is suitable both the heath-shrinking sealingkit and cold sealing kit (BASE A)

CLOSURE MSC AC COMPONENTS AND CONFIGURATION



CLAMP MSC LOCKING CLIP \varnothing 285mm



MSKIT MST TRAY SPLICE CAPACITY 96 F.O.



A BASE Ø 247 mm OVAL PORT 6 ROUND

FOR **FOCUS ODCKIT*** COLD AND HEATH PORT

www.optotec.com











All the information included in this document, including drawings, illustration and patterns have to be considered reliable; they are registered and owned by Optotec S.p.A, therefore it is strictly forbidden to use them without our previous authorization. However, Optotec makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. Optotec obligations shall only be as set forth in Optotec Standard Terms and Conditions of Sale for this product and in no case will Optotec be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of Optotec products should make their own evaluation to determine the suitability of each such product for the specific application.

Optotec S.p.A. Via Zenale, 44 20024 Garbagnate Milanese (MI) - Italy P.IVA 10730100152 | Telephone: +39 02 99515.1 | FAX: +39 02 99515.222 | info@optotec.it

1 OPT-B-2020-05-MSC-AC-ENG





ORDERING INFORMATION FOR FOCUS MSC AC CLOSURES

OPTOTEC PN. EXAMPLE:

FOCUS	MSC	A	C	H	1
OPTOTEC PRODUCT LINE	SERIE NAME	BASE TYPE	DOME TYPE	HOLDER TYPE	n° OF TRAY FOCUS- MSCKIT-MST TYPE
FIBER OPTIC CONNECTING UNIT SYSTEM	MSC = Mass Splice Closure	Α	C	Н	UP TO 8
				C	UP TO 8

FOCUS CLOSURES SPLICE CAPACITY


FOCUS CLOSURES SPLICE DEPENDING ON THE QUANTITY OF **FOCUS MSCKIT MST TRAYS INSTALLED.** ALL CLOSURES ARE USEABLE TO INSTALLED UP TO MAX 8 TRAYS.

FOCUS MSC KIT -

FOCUS MSCKIT MST H TRAY WITH H HOLDER

FIBERTERM H


FOR 96 HEATHSHRINKABLE FIBERTERM PROTECTIONS.



SPACE ALSO FOR PLC LODGE

FOCUS MSCKIT MST C TRAY WITH CHOLDER

MST-C TRAY FOR 96 MECHANICAL FIBERCLIP PROTECTIONS.



SPACE ALSO FOR PLC LODGE

ORDERING INFORMATION

ESEMPIO CODICE OPTOTEC:

FOCUS	MSCKIT	MST	H
OPTOTEC PRODUCT LINE	SERIE NAME	TRAY TYPE	HOLDER TYPE
FOCUS	MSCKIT	MST	Н
			C



For managing in and out cables, choose Optotec sealing KITS; FOCUS ODCKIT for heath or cold management, heathshrinkable.

PACKAGING

PRODUCT NAME	PACKAGING TYPE		GROSS		
					WEIGHT (kg.)
FOCUS-MSC-AC-H1	Carton box	300	300	800	6
FOCUS-MSC-AC-C1	Carton box	300	300	800	6
FOCUS-MSCKIT-MST-H	Carton box	500	150	20	0,44
FOCUS-MSCKIT-MST-C	Carton box	500	150	20	0,44



www.optotec.com

All the information included in this document, including drawings, illustration and patterns have to be considered reliable; they are registered and owned by Optotec S.p.A, therefore it is strictly forbidden to use them without our previous authorization. However, Optotec makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. Optotec' obligations shall only be as set forth in Optotec' Standard Terms and Conditions of Sale for this product and in no case will Optotec be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of Optotec products should make their own evaluation to determine the suitability of each such product for the specific application.

Optotec S.p.A. Via Zenale, 44 20024 Garbagnate Milanese (MI) - Italy P.IVA 10730100152 | Telephone: +39 02 99515.1 | FAX: +39 02 99515.222 | info@optotec.it

2 OPT-B-2020-05-MSC-AC-ENG